

Climbing Holds Casting Silicone

Product Description:

Climbing Holds Casting Silicone is wonderful to make molds either with simple or intricate patterns for Rock climbing holds, climbing walls, climbing holds etc. With good resistance to heat, deformation, acid & alkali and expansion, finished silicone molds serve very good performance in reproduction process with every fine detail on designing models.





Appearance:

Part A: Silicone Rubber is an white liquid

Part B: Catalyst is an non-toxic and odorless liquid in transparent color.

ATT: we can provide catalyst of **Fast, Medium, Slow** for hot ,cold, warm season.



Web:www.ottsilicone.comPage 1Email:sz@ottsilicone.comTel:+86-020-86819712Email:gz@ottsilicone.com



Guangzhou OTT New Materials Co., Ltd.

Features:

- ♦ Amazing fluidity and easy to operate
- ♦ Delicate design available
- ♦ Non Oily
- ♦ Non white stick pot
- ♦ Non-toxic and odorless catalyst Provided
- ♦ Easy de-molding
- ♦ Excellent tension and tear strength
- ♦ High performance in duplication
- ♦ Excellent resistance to weather, temperature, aging, acid & aging-Proofing.

Model Code: \$820#, \$825#, \$830#

Technical Data:

Typical general characteristics	Inspection Method	Value		
Product data (Catalyzed A+B)		S820	S825	S830
Hardness	Shore A	20±2	25±2	30±2
Mix Ratio	A:B	100:3	100:3	100:3
Color	/	White	White	White
Pot life	25 °C (77F)	30-50mins	30-50mins	30-50mins
Curing time	25 °C (77F)	3- 5hrs	3- 5hrs	3- 5hrs
Viscosity	mPa.s	13000±3000	15000±3000	18000±3000
Tear-Strength	kg/cm	≥28	≥28	≥28
Tensile -Strength	M.pa	≥4.5	≥4.5	≥4.5
Elongation	%	≥500	≥500	≥420
Shrinkage	%	≤0.2	≤0.2	≤0.2

Notes: The data are based on the operation under room temperature of 25 $^{\circ}$ C.

Web:www.ottsilicone.comPage 2Email:sz@ottsilicone.comTel:+86-020-86819712Email:gz@ottsilicone.com



Guangzhou OTT New Materials Co., Ltd.

Packing:

Part A for silicone: 1kg, 5kg, 10kg, 20kg, 25kg, 200kg, Vacuumed Packing.

Part B for catalyst: 30g, 50g, 100g, 150g, 200g, 250g, 1kg.



Storage & Shelf Life:

1Year at least, stored in a cool and dry place under room temperature 25°C

Operation Method:

Both Pouring or brushing operation methods for our Climbing Holds casting silicone are available. You can chose the best one as your preference, we can provide thixotropic agent for Brushable.



Caution - Safety First !!!

- 1. Read the material safety data sheet(MSDS) before use.
- 2. Keep Out Of Reach Of Children.
- 3. Be careful. Use only with adequate ventilation. Contact with skin and eyes may cause irritation. Flush eyes with water for 15mins and seek immediate medical attention. Remove from skin with water-less hand cleaner followed by soap & water.



Web:www.ottsilicone.comPage 3Email:sz@ottsilicone.comTel:+86-020-86819712Email:gz@ottsilicone.com